

SUBMITTAL SHEET

PEX-A

Brass Fittings F1960

PureLink PEX-A Brass Fittings are used for making junctions or directional changes with PEX-A pipe constructed potable water systems.

All PureLink PEX-A Brass Fittings comply with the U.S. Safe Water Drinking Act (SDWA) and the 2011 U.S. Reduction of Lead in Drinking Water Act by containing equal to or less than 0.25% lead.

All PureLink PEX-A Brass Fittings have barb ends unless otherwise noted. PureLink PEX-A Brass Fittings can be used with PureLink PEX-A or Uponor ProPEX™ tubing. Fittings may be installed in concrete, gypsum-based lightweight concrete, sand, asphalt, in or under wood flooring, or behind wallboard or plaster.

Specifications:

Use PureLink PEX-A Brass Fittings with PureLink PEX-A pipe and fasten to pipe using PureLink Expansion Sleeves with PureLink PEX-A Tools. Follow all instructions included with PureLink tools, fittings, and fasteners.

Features:

- Designed exclusively for use within Type A PEX piping systems
- Full-flow design for maximum water output
- Larger internal diameter results in a 25% greater flow rate within the system
- Constructed of lead free dezincification resistant (DZR) brass for superior reliability and strength
- A cold-expansion tool (sold separately) is required for installation
- Must be secured in place using PureLink PEX-A sleeves or other PEX-A expansion sleeves/rings
- Go/No-Go gauges are never required
- To ensure secure connections every time, fittings cannot be dry fit
- Suitable for new construction, repairs, and remodels

Standards / Certifications:



- Rated 200° F and 200 psi
- Meets ASTM F876/F877/F2023/F1960
- Meets ANSI/NSF 61 & 14
- Not compatible with PEX-B pipe, crimp style (ASTM 1807) or pinch clamp (ASTM 2098) piping systems
- Meets CSA B137.5
- cNSFus-pw
- cUPC

Installation:

To cut PEX tubing, use a PEX tubing cutter and cut at a 90° angle. Clear the cut end of any burrs or debris. Place expansion sleeve on end of tubing. Insert tool head into tubing end and expand. Immediately remove tool and insert fitting into pipe to shoulder. Pipe may take up to two minutes to fully seal fitting.

Compatible with Uponor (Wirsbo) ProPEX™. (ProPEX™ is a trademark of Uponor [Wirsbo].)

Job Name:	
Job Location:	
Engineer:	
Contractor:	
Tag:	
PO Number:	
Representative:	



Couplings						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXC12	1/2"	1.54	0.67	0.67	0.06	
WEPXC1234	1/2" x 3/4"	1.79	1.02	1.02	0.10	
WEPXC34	3/4"	2.05	0.95	0.95	0.12	
WEPXC341	3/4" x 1"	2.29	1.22	1.22	0.19	
WEPXC1	1"	2.54	1.20	1.20	0.23	



90° Elbows						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXDEE12	1/2" PEX-A Barb x 1/2" FPT	2.22	1.26	1.95	0.19	
WEPXDEE3412	3/4" PEX-A Barb x 1/2" FPT	2.47	1.45	1.92	0.22	
WEPXDEE34	3/4" PEX-A Barb x 3/4" FPT	2.80	1.43	2.18	0.34	
WEPXE12	1/2"	1.51	1.51	0.65	0.11	
WEPXE1234	1/2" x 3/4"	1.70	1.58	0.79	0.13	
WEPXE34	3/4"	2.00	2.00	0.83	0.19	
WEPXE1	1"	2.50	2.50	1.06	0.39	
WEPXFAE12	1/2" PEX-A Barb x 1/2" FPT Swivel	1.53	1.69	1.30	0.12	



CPVC and PVC Adapters						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXCPVC12	1/2" x 1/2" CPVC	1.50	1.06	1.06	0.08	
WEPXCPVC34	3/4" x 3/4" CPVC	1.75	1.50	1.50	0.15	



Press Adapters						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
EPXPR1212	1/2" x 1/2" Press	1.88	0.88	0.88	0.08	
EPXPR3434	3/4" x 3/4" Press	2.00	1.19	1.19	0.13	
EPXPR11	1" x 1" Press	2.50	1.50	1.50	0.21	



Tees						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXT12	1/2"	2.08	1.54	0.63	0.13	
WEPXT121234	1/2" x 1/2" x 3/4"	2.60	1.72	0.87	0.17	
WEPXT341212	3/4" x 1/2" x 1/2"	2.58	1.56	0.87	0.17	
WEPXT341234	3/4" x 1/2" x 3/4"	2.84	1.90	0.85	0.21	
WEPXT343412	3/4" x 3/4" x 1/2"	2.72	1.68	0.87	0.19	
WEPXT34	3/4"	3.27	1.86	0.84	0.26	
WEPXT1112	1" x 1" x 1/2"	3.31	1.96	1.11	0.33	
WEPXT1134	1" x 1" x 3/4"	3.55	2.17	1.11	0.37	
WEPXT11	1"	4.10	2.33	1.11	0.52	



Female Adapters						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXFA12	1/2" x 1/2" FPT	1.33	0.97	0.97	0.08	
WEPXFA12S	1/2" x 1/2" FPT	1.52	1.38	1.38	0.06	
WEPXFA1234	1/2" x 3/4" FPT	1.45	1.19	1.19	0.15	
WEPXFA3412	3/4" x 1/2" FPT	1.60	0.95	0.95	0.11	
WEPXFA34	3/4" x 3/4" FPT	1.59	1.22	1.22	0.14	
WEPXFA34S	3/4" x 3/4" FPT	1.73	1.18	1.18	0.20	
WEPXFA341	3/4" x 1" FPT	1.82	1.49	1.49	0.29	
WEPXFA1	1" x 1" FPT	1.93	1.50	1.50	0.24	
WEPXFA6	1 1/4" x 1 1/4" FPT	2.60	2.09	2.09	0.51	
WEPXFA7	1 1/2" x 1 1/2" FPT	2.98	2.41	2.41	0.81	
WEPXFS12	1/2" x 1/2" FS	1.29	0.75	0.75	0.05	
WEPXFS1234	1/2" x 3/4" FS	1.60	1.00	1.00	0.09	
WEPXFS34	3/4" x 3/4" FS	1.83	1.00	1.00	0.11	
WEPXFS341	3/4" x 1" FS	1.99	1.30	1.30	0.17	
WEPXFS1	1" x 1" FS	2.18	1.36	1.36	0.18	
WEPXFS6	1 1/4" x 1 1/4" FS	2.65	1.54	1.54	0.38	
WEPXFS7	1 1/2" x 1 1/2" FS	2.91	1.85	1.85	0.51	
WEPXFS8	2" x 2" FS	3.61	2.36	2.36	0.94	



Male Adapters						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXMA12	1/2" x 1/2" MPT	1.52	0.87	0.87	0.08	
WEPXMA1234	1/2" x 3/4" MPT	1.66	1.06	1.06	0.13	
WEPXMA3412	3/4" x 1/2" MPT	1.76	0.91	0.91	0.11	
WEPXMA34	3/4" x 3/4" MPT	1.80	1.06	1.06	0.14	
WEPXMA341	3/4" x 1" MPT	1.97	1.33	1.33	0.23	
WEPXMA134	1" x 3/4" MPT	2.14	1.34	1.34	0.20	
WEPXMA1	1" x 1" MPT	2.16	1.33	1.33	0.23	
WEPXMA6	1 1/4" x 1 1/4" MPT	2.96	1.95	1.95	0.65	
WEPXMA7	1 1/2" x 1 1/2" MPT	3.39	2.19	2.19	0.87	
WEPXMA8	2" x 2" MPT	3.86	2.80	2.80	1.35	
WEPXMS12	1/2" x 1/2" MS	1.40	0.67	0.67	0.05	
WEPXMS1234	1/2" x 3/4" MS	1.67	0.87	0.87	0.09	
WEPXMS34	3/4" x 3/4" MS	1.91	0.94	0.94	0.11	
WEPXMS341	3/4" x 1" MS	2.05	1.22	1.22	0.15	
WEPXMS1	1" x 1" MS	2.28	1.22	1.22	0.20	
WEPXMS6	1 1/4" x 1 1/4" MS	2.62	1.37	1.37	0.29	
WEPXMS7	1 1/2" x 1 1/2" MS	3.00	1.62	1.62	0.42	
WEPXMS8	2" x 2" MS	3.83	2.12	2.12	0.98	



Drop Ear Tees						
Part #	Size (CTS)	L	H	D	Wt (lbs.)	
WEPXDET12	1/2" x 1/2" x 1/2" FPT	2.5	1.50	1.88	0.22	
WEPXDET34	3/4" x 3/4" x 3/4" FPT	3.25	1.75	2.13	0.38	

